



GK2226W

by Burndy
Catalog ID: GK2226W

Prop 65 Notice

WIRE: 4 SOL 2/0 STR CU

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
Type	Three Cables to Rod or Tube
UPC	781810135204
UPC 12 Digit	7818101352044

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height inch	6.38 in
Dimension - Width fraction	6-2/3 in
Dimension - Width inch	6.69 in
Dimension - Width mm	170 mm

Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	4;4 1/2
Conductor - Copper Str Size Range	5-2/0
Conductor - Copper Tube Std Size	3
Conductor - Copper Tube Std Size Range	3

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)