



GKA28SB

by Burndy
Catalog ID: GKA28SB

Prop 65 Notice

ACCOMMODATES: 1 STR - 4/0 STR RECOMMENDED TORQUE: 275 IN/LB
SILICON BRONZE HARDWARE

Product Details

General

Installation Torque Recommended in-lb	275 LBS/in
Material	Copper Alloy
Material Type - Screw	Steel - Stainless
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	KA-LUG™
UPC	781810569603
UPC 12 Digit	7818105696033

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Height inch	1.25 in
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - N inch	0.44 in
Dimension - Pad Width inch	0.94 in

Conductor Related

Conductor - Copper Str Size	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	1 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)