

## GKA4C

by Burndy  
Catalog ID: GKA4C

Prop 65 Notice

Copper Alloy Direct Burial Terminal, #14 Sol. - #4 Str., 1.13 in L.

Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, One-Piece Forged Body Construction Insures Mechanical Integrity In An Underground Environment, Supplied With A Stainless Steel Headless Screw, To Be Assembled With TMH 323 Stainless Steel Hardware Kit, Length: 1.13 IN, Width: 0.54 IN, Dimension K: 0.28 IN, Dimension B: 0.46 IN, Height: 0.71 IN



## Product Details

### General

Application	For Direct Burial Applications In Earth Or Concrete
Installation Torque Recommended in-lb	45 LBS/in
Material	Copper Alloy
Material Type - Screw	Steel - Stainless
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GKA
UPC	781810100998
UPC 12 Digit	7818101009988

### Dimensions

Dimension - B Length inch	0.46 in
Dimension - Height inch	0.71 in
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.13 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	0.54 in

### Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)