



GL2626T4

by Burndy
Catalog ID: GL2626T4

Copper Alloy Mechanical Grounding Connector

Product Details

General

| | |
|---------------------------------------|------------------------|
| Installation Torque Recommended in-lb | 240 LBS/in |
| Material | Copper Alloy |
| Material Type - Screw | DURIUM™ Silicon Bronze |
| Physical Attribute - Screw Type | Hexagonal Bolt |
| Plated | N |
| Plating Type | Unplated |
| UPC | 781810079416 |
| UPC 12 Digit | 7818100794166 |

Dimensions

| | |
|---|----------|
| Dimension - B Length inch | 1.69 in |
| Dimension - D inch | 1.94 in |
| Dimension - F Width Center to Center inch | 1.00 in |
| Dimension - Length Side B inch | 1.88 in |
| Dimension - Pad Width inch | 0.94 in |
| Dimension - Width fraction | 1-3/4 in |
| Dimension - Width inch | 1.75 in |
| Dimension - Width mm | 44 mm |

Conductor Related

| | |
|-------------------------------------|---|
| Conductor - Copper Solid Size | 4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG |
| Conductor - Copper Solid Size Range | 4 AWG-2/0 AWG |
| Conductor - Copper Str Size | 4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG |
| Conductor - Copper Str Size Range | 4 AWG-2/0 AWG |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |

| | |
|------------------------------------|-------|
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 12 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)