



## GL2929TN

by Burndy  
Catalog ID: GL2929TN

Prop 65 Notice

Tin plated Copper Alloy Mechanical Grounding Connector

## Product Details

### General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin Plated
UPC	781810227336
UPC 12 Digit	7818102273366

### Dimensions

Dimension - B Length inch	2.22 in
Dimension - D inch	2.25 in
Dimension - F Width Center to Center inch	1.25 in
Dimension - Length Side B inch	2.44 in
Dimension - Pad Width inch	1.22 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm

### Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2/0 AWG-250 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)