

GP10

by Burndy
Catalog ID: GP10

Prop 65 Notice

Gasoline Hydraulic Pump, 4 HP, Reservoir Volume 8 qts, 10000 psi.

- Heavy duty gasoline engine
- Sturdy steel roll cage design
- Manual control valve
- Quick disconnect hydraulic coupler
- 8 quart reservoir
- Oil level inspection window

Features: The GP Series Gasoline Engine Driven Hydraulic Pump Is A Heavy-Duty Design That Is Rugged And Portable, Supplied With A Four (4) HP Engine, The Pump Operates All BURNDY Remote Compression Heads And Cable Cutters, All GP Style Pumps Have A Built-In, Factory Pre-Set, Automatic Pressure Release Overload Valve With A Definite Pulsing And Recycling To Signal The Completion Of A Crimp, The Manual Control Valve Allows User To Jog And Hold Due To The Unique Check Valve Design That Keeps Pressure In The Output Line Until Retracted, Portable Pump With Sturdy Steel Roll Cage, Durable Heavy-Duty Four (4) HP Engine For All HYPRESS Applications And Long Life Expectancy, Manual Control Valve Permits Easy Control Of Crimping Or Cutting Operations, Fast Hose Assembly With Quick Disconnect Pressure Matched Hydraulic Couplers, Ample Hydraulic Capacity With (8) Quart Reservoir, 5-Year Limited Warranty, Reservoir Volume: 8 QT, Weight: 64-1/4 LB Dry Pump And Motor, 77-3/4 LB Overall, Replacement Fluid: Alfluid5 year limited warranty



Product Details

General

Application	For Y34BH, Y35BH, Y35BH-4, Y39BH, Y45, Y46, Y46C, Y60BHU, Y60BHU-D, Y750BH, Y750BH-2, RHCC Series Cutters
Power Source	4 HP, 4 Cycle Engine
Sub Brand	MECHANICAL CONNECTOR
Tool Type	Gas Hydraulic Pump
Type	Pumps
UPC	781810492758
UPC 12 Digit	7818104927588

Dimensions

Height	22.25 in
Length	21 in
Weight	78 lb
Width	16 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)