



## GP1726RT

by Burndy  
Catalog ID: GP1726RT

Prop 65 Notice

ACCOMMODATES ONE OR ANY COMBINATION OF TWO CONDUCTORS  
IN RANGE: #6-2/0 STR CU TORQUE: 245 LB-IN

### Product Details

#### General

Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Pedestal Type	Round;Square
Plated	N
Plating Type	Unplated
UPC	781810141779
UPC 12 Digit	7818101417799

#### Dimensions

Dimension - Height inch	3.86 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Width inch	3.22 in
Dimension - Width mm	82 mm

#### Conductor Related

Conductor Size	#6 AWG - 2/0 AWG STR
Number Of Conductors	1;2

#### Certifications and Compliance

Certification - CSA Approved	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)