



GP1826

by Burndy
Catalog ID: GP1826

Prop 65 Notice

Mechanical grounding connector, 2" Pipe Size, 2" Rod Size, 4 SOL - 2/0 STR Wire Size, 240 LBS/in Installation Torque.

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	257
UPC	781810079171

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	2.75 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width fraction	3-11/16 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

Conductor Related

Conductor - Rod Size	2 in
Conductor Size	#4 Sol AWG - 2/0 Str AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)