



## GP1829

by Burndy  
Catalog ID: GP1829

Prop 65 Notice

Mechanical grounding connector, 2" Pipe Size, 2" Rod Size, 2/0 SOL - 250 kcmil Cable Range, 240 LBS/in Installation Torque.

## Product Details

### General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	257
UPC	781810124734

### Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	2.75 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - Width fraction	3-11/16 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

### Conductor Related

Conductor - Rod Size	2 in
Conductor Size	2/0 AWG Sol - 250 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)