



GP654CG1

by Burndy
Catalog ID: GP654CG1

Prop 65 Notice

Raised Floor Grounding Clamp, #8 Sol. - 4 Str., 1.31 in L, 2.38 in.

Features: Accepts 1 Or 2 Ground Conductors, Requires Less Connectors To Install Signal Reference Grid, Made Of Copper Alloy, DURIMUM U-Bolts, Nuts And Lockwashers, Provides A Low Impedance Ground Path For Maximum Performance, Grounds All Pedestals (Round Or Square), Will Handle From 3/4 IN To 1 IN Round Or Square, Ease Of Installation, Serves 3 Needs, 1. Signal Reference Grid, 2. Static Ground, 3. Fault Current Ground, Connectors Solves All Possible Grounding Problems Found In Computer Applications Today, UL467 Listed, Dimension B: 1.5 IN, Raised Floor: Yes, Pedestal Type: Round, Square, Ground Rod Size: 3/4 - 7/8 IN, Tube (ips) Size: 3/4 - 1 IN, Installation Torque: 240 IN-LB, Width: 2.38 IN, Length: 1.31 IN

Product Details

General

Application	For Raised Floor Computer Grounding Applications
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material - Hardware	DURIMUM™ Silicon Bronze
Pedestal Type	Round;Square
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GP-G1
U Bolt Type	UB222
UPC	781810828007
UPC 12 Digit	7818108280077

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.50 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60 mm

Conductor Related

Conductor - Copper Solid Size Range	8 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor Size	#8 AWG Sol - #4 AWG Str
Number Of Conductors	1;2

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)