



GQ261

by Burndy
Catalog ID: GQ261

Prop 65 Notice

Cu Ground Connector, #4 - 2/0 AWG Str Cu , above 6" IPS, Cable to Tube

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	399;291
UPC	781810233764
UPC 12 Digit	7818102337644

Dimensions

Bolt Size	1/2 in
Dimension - Height inch	6.41 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - Width inch	2.44 in
Dimension - Width mm	62 mm

Conductor Related

Conductor - Copper Str Size Range	4 AWG-2/0 AWG
Conductor Size	#4 AWG Str - 2/0 AWG Str
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)