



GRC58916CF

by Burndy
Catalog ID: GRC58916CF

Prop 65 Notice

Cu Grounding Rod Connector, Suitable for Direct Burial, 9/16 IN Stud, Cu Cable to Rod, 5/8 IN Rod (Run), 10 AWG Sol - 1 AWG Str. (Tap), Hex Head Bolts Available

Product Details

General

Material	Copper Alloy
Plated	N
Plating Type	Unplated
UPC	781810662090
UPC 12 Digit	7818106620900

Dimensions

Bolt Size	9/16 in
Dimension - B Length inch	0.57 in
Dimension - Height inch	2.18 in
Dimension - Width inch	0.92 in
Dimension - Width mm	23 mm

Conductor Related

Conductor - Rod Size	5/8 in
Conductor Size	#10 AWG Sol - #1 AWG Str
Conductor Type	<ul style="list-style-type: none"> Rod-Size CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)