



GRL4

by Burndy
Catalog ID: GRL4

Prop 65 Notice

Copper Alloy Light Duty Economical Ground Rod Clamp, 2-10 AWG, 1/2-Rod Size.

Features: UL467 Listed, Acceptable For Direct Burial, Economical, Ground Rod Size: 1/2 IN

Product Details

General

| | |
|--------------|----------------------|
| Application | For Direct Burial |
| Material | Copper Alloy |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | MECHANICAL CONNECTOR |
| Type | GRL, Light Duty |
| UPC | 781810051818 |
| UPC 12 Digit | 7818100518188 |

Conductor Related

| | |
|-----------------------------------|------------------|
| Conductor - Copper Str Size Range | 10 AWG-2 AWG |
| Conductor - Rod Size | 1/2 in |
| Conductor Size | #2 AWG - #10 AWG |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)