



## GRL6

by Burndy  
Catalog ID: GRL6

Prop 65 Notice

Light Duty Economical Ground Rod Clamp,CU, 2-10 AWG, 3/4" Rod Size.

Features: UL467 Listed, Acceptable For Direct Burial, Economical, Ground Rod Size: 3/4 IN

## Product Details

### General

Application	For Direct Burial
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRL, Light Duty
UPC	781810051832
UPC 12 Digit	7818100518322

### Conductor Related

Conductor - Copper Str Size Range	10 AWG-2 AWG
Conductor - Rod Size	3/4 in
Conductor Size	#2 AWG - #10 AWG

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)