

GSTUD12HY

by Burndy
Catalog ID: GSTUD12HY

Prop 65 Notice

Structural Steel Grounding Connector, 1/0 AWG 1/2" Rod, Copper Coated, Nickel Plated

- May be welded to steel surfaces quickly and easily
- No disk grinding needed
- Knurled surface for better gripping
- Copper plated
- May be installed during adverse weather conditions



Product Details

General

Material	Steel
Plated	Y
Plating Type	Nickel
Trade Name	VERSITAIL™
UPC	781810274187
UPC 12 Digit	7818102741877

Dimensions

Dimension - B Length fraction	25/49 in
Dimension - B Length inch	0.51 in
Dimension - D inch	1.25 in
Dimension - Ground Rod Size	1/2 in
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.80 in
Physical Attribute - Tongue Angle	45 Degree

Conductor Related

Conductor - Copper Str Size Range	1/0 AWG
Conductor - Rod Size	1/2 in
Conductor - Rod Size Range	1/2 in
Conductor Type	<ul style="list-style-type: none"> • Rod-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)