



## GX2626

by Burndy  
Catalog ID: GX2626

Prop 65 Notice

Mechanical Grounding Connector, Cable Cross Connection, 4 AWG (Sol.) - 2/0 AWG (Str.) ( Run), 4 AWG (Sol.) - 2/0 AWG (Str.) ( Tap), 3/8" Stud.

Features: High Copper Alloy Ground Connector For Cross Connecting A Wide Range Of Cable, The High Copper Alloy Cast Body, DURIUM U-Bolts, Nuts, And Lockwashers Make The GX Suitable For Burial In Soil Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Length: 1-3/4 IN, Installation Torque: 240 IN-LB, Height: 2-1/2 IN, Width: 1-3/4 IN

## Product Details

### General

Application	For Cross Connecting A Wide Range Of Copper Cable, Direct Burial In Earth Or Concrete
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GX
U Bolt Type	354
UPC	781810991695
UPC 12 Digit	7818109916955

### Dimensions

Dimension - Height fraction	2-1/2 in
Dimension - Height inch	2.75 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width fraction	1-2/3 in
Dimension - Width inch	1.69 in
Dimension - Width mm	43 mm

### Conductor Related

Conductor - Copper Solid Size A	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size A Range	4-3/0
Conductor - Copper Solid Size B	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size B Range	4-3/0
Conductor - Copper Str Size A	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size A Range	5-2/0

Conductor - Copper Str Size B	4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	4-2/0
Conductor - Copper Tube Std Size	0.375
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size A</li> <li>• CU C Solid-Size A</li> <li>• CU C Str-Size B</li> <li>• CU C Solid-Size B</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)