



GZ2612

by Burndy
Catalog ID: GZ2612

Prop 65 Notice

Mechanical Grounding Connector, For Copper Cable to Bar, 3 AWG (Str) - 2/0 (Str), 1/2" Stud.

Features: High Copper Alloy Ground Connector For Joining A Wide Range Of Cable To 1/4 IN Thick Bar, Cable Is Gripped By Curving It Around The Clamping Bolt In Connector Groove, UL467 Listed, The High Copper Alloy Cast Body And DURIMUM Bolts, Nuts, And Lockwashers Make Them Suitable For Direct Burial In Concrete Or Ground, Installation Torque: 480 IN-LB, Width: 1-3/4 IN, Height: 2-1/8 IN, Bar Thickness: 1/4 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Bar, Direct Burial In Concrete Or Ground
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GZ
UPC	781810232125
UPC 12 Digit	7818102321255

Dimensions

Dimension - Height fraction	2-1/8
Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.88 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.75 in
Dimension - Width mm	44 mm

Conductor Related

Conductor - Copper Str Size	3;2;1;1/0;2/0
Conductor - Copper Str Size Range	3-2/0

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)