



GZ2658T4

by Burndy
Catalog ID: GZ2658T4

Prop 65 Notice

Mechanical Grounding Connector, 3 AWG (Str) - 2/0 AWG (Str), 5/8" Stud, Bar Thickness 1/4" -1/2"

Product Details

General

Installation Torque Recommended in-lb	660 in-lb
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
UPC	781810219911
UPC 12 Digit	7818102199111

Dimensions

Bolt Size	5/8 in
Dimension - Bar Thickness inch	0.25 in
Dimension - Bar Thickness mm	6 mm
Dimension - Height inch	2.25 in
Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.88 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.75 in
Dimension - Width mm	44 mm

Conductor Related

Conductor - Copper Str Size	3;2;1;1/0;2/0
Conductor - Copper Str Size Range	3-2/0
Conductor Range	#3 AWG (Str) to #2/0 AWG (Str)

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)