



## GZ2958

by Burndy  
Catalog ID: GZ2958

Prop 65 Notice

Mechanical Grounding Connector, 3/0 AWG (Str) - 250 kcmil, 5/8" Stud

## Product Details

### General

Installation Torque Recommended in-lb	660 in-lb
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
UPC	781810260784
UPC 12 Digit	7818102607844

### Dimensions

Bolt Size	5/8 in
Dimension - Bar Thickness inch	0.25 in
Dimension - Bar Thickness mm	6 mm
Dimension - Height fraction	2-1/2
Dimension - Height inch	2.50 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.34 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.18 in
Dimension - Width mm	55 mm

### Conductor Related

Conductor - Copper Str Size	3/0;4/0;250
Conductor - Copper Str Size Range	3/0-250
Conductor Range	#3/0 AWG (Str) - 250 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	6
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)