



HFB334N

by Burndy
Catalog ID: HFB334N

Prop 65 Notice

Substation Connectors

Product Details

General

| | |
|----------------|---------------|
| Application | Substation |
| Connector Type | Tap |
| Material | Copper |
| Plated | N |
| Plating Type | Bright Dipped |
| UPC | 781810005767 |
| UPC 12 Digit | 7818100057677 |

Dimensions

| | |
|---|---------|
| Dimension - B Length inch | 3.00 in |
| Dimension - F Width Center to Center inch | 1.75 in |
| Dimension - L Length Overall mm | 178 mm |
| Dimension - Length Overall inch | 7.00 in |
| Dimension - N inch | 0.62 in |
| Dimension - Pad Width inch | 3.00 in |
| Dimension - Pin Diameter fraction | 3 in |
| Dimension - Pin Diameter inch | 3.00 in |

Electrical Ratings

| | |
|--------------|--------|
| Rating - KVA | 230 kV |
|--------------|--------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 8 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)