



HIW716ENFKIT3

by Burndy
Catalog ID: HIW716ENFKIT3

Prop 65 Notice

HYDRAULIC IMPACT WRENCH HIW716ENF WITH 3/8" NPT Male and Female Coupling, Size: 9.03"X7.99"X3.21", Opt. Pressure: 750-2000PSI

- Industry exclusive dual torque selector spool to switch between 200 and 515 ft-lb torque settings
- 7/16" tri-ball quick chuck for fast changing of bits, sockets, etc.
- Cartridge style vales for greater accuracy and economical servicing
- Dual spool operation allows for use in Open or Closed central hydraulic systems

5 year limited warranty

Product Details

General

Operation	OPEN / CLOSED OPTION
Trade Name	ENFORCER®
UPC	781810509845
UPC 12 Digit	7818105098455

Dimensions

Height	3.21 in
Length	9.03 in
Weight	5.95 lb
Width	7.99 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)