



HIW716ENF

by Burndy
Catalog ID: HIW716ENF

Prop 65 Notice

Hydraulic Impact Wrench Variable Torque, 7.80 in L, 3.10 in W.

- Industry exclusive dual torque selector spool to switch between 200 and 515 ft-lb torque settings
- 7/16" tri-ball quick chuck for fast changing of bits, sockets, etc.
- Cartridge style vales for greater accuracy and economical servicing
- Dual spool operation allows for use in Open or Closed central hydraulic systems

Features: Industry exclusive torque selector. Dual torque selector spool allows users to switch between 200 and 515 ft-lb torque settings, 7/16 Tri-ball quick chuck. Allows users to quickly change bits,sockets or other hardware adaptors, CNC Machined billet aluminum.Provides superior strength, reliability and makes for the lightest tool in its class. Also provides for tighter tolerancing to ensure higher quality.Cartridge style valves.Provides for greater accuracy and more economical servicing, Dual spool operation.Allows tool to be used in either an OPEN or CLOSED center hydraulic system.5 year limited warranty

Product Details

General

Application	Loosening/ Tightening
Installation Torque Recommended in-lb	6180 in-lbs
Sub Brand	ENFORCER
Tool Type	Low Pressure Hydraulic Impact Wrenches
Trade Name	ENFORCER®
Type	Variable Torque Option
UPC	781810472903
UPC 12 Digit	7818104729033

Dimensions

Height	9.03 in
Length	7.81 in
Weight	5.95 lb
Width	3.21 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)