



HIW716MAGKIT1

by Burndy
Catalog ID: HIW716MAGKIT1

Prop 65 Notice

HIW716MAG Hydraulic Impact Wrench with Flat Face Couplers, Optimal Pressure: 1000-2000PSI, Flow Range: 4-12 GPM, Operation: Open/Closed option

- Aircraft grade 7075-T6 extruded Aluminum body and forged handle for added strength
- CNC machining produces tighter tolerances contributing to increased efficiency, repeatability and flow optimization
- Machined steel sleeve and hardened spool increase wrench efficiency by preventing hydraulic fluid "blow by"
- Balanced weight in assembled configuration
- Reverse flow protection to prevent reverse hook-ups
- Dual spool selector for Open and Closed Center use
- For Use With: Utility pole hardware & Auger drill bits

5 years

Product Details

General

Installation Torque Recommended in-lb	6600 in-lb
Tool Type	Low Pressure Hydraulic Impact Wrenches
UPC	781810568347
UPC 12 Digit	7818105683477

Dimensions

Height	9.6 in
Length	9.0 in
Weight	7.6 lb
Width	3.6 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)

