



HSIC350FR

by Burndy
Catalog ID: HSIC350FR

Heavy wall heat shrinkable end cap, 3.50" ID Min.(Exp.), 1.18" ID Max.(Rec.), 1250 Kcmil AWG, Polyolefin, Thick Wall, Black, Shrink ratio-3:1, 600V

Product Details

General

Color	Black
Material	Polyolefin
UPC	781810266571

Conductor Related

Conductor Range	1250 Kcmil
-----------------	------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	7500
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)