



HTP3

by Burndy
Catalog ID: HTP3

Prop 65 Notice

Hydraulic Trash Pump, Weight: 40 lbs., Pump capacity: 500 GPM, Motor: Gear Motor.

- Self-lubricating design
- Totally submersible
- Can run dry without damage
- Open/Closed Center operation

Features: The HP3 And HTP3 Hydraulic Submersible Pumps Are Designed To Reliably Pump Large Volumes Of Liquids And Solids (Per Specifications), HP And HTP Models Are Durable And Offer A Very High Performance-To-Weight Ratio, These Pumps Are Self-Lubricating, Utilizing The Hydraulic Fluid In A Closed Loop To Ensure Consistent, Reliable Lubrication, The Units Can Be Run Dry As They Do Not Require Water For Cooling Purposes Whether Submersed Or Not, The High Output And Compact Nature Of These Pumps Make Them Ideal For Pumping Out Vaults, Trenches, Ditches, Ponds, Tanks, Pools, Etc, In A Multitude Of Industries Including Agriculture, Construction, Mining, Utilities, Public Works, Departments Of Transportation, And More, Totally Submersible, Pumps Solids Without Blockage Or Damage, Self Lubricating Design, Cast Aluminum Pump Body, Double-Sealed Hydraulic Motor Shaft Protects Hydraulic Source From Water, Thumb Screw Secured Lid So Cover Is Easy To Remove Without Special Tools, Provided With Whip Hoses, High Impact, Abrasion Resistant Liner, 5-Year Limited Warranty, Motor: Gear, Maximum Lift: 40 FT, Accessories: HOSE325- 25 FT Long Hose, HOSE350- 50 FT Long Hose, Number Of Port: 1/2 IN X 14 (#8), NPT (F), Maximum Back Pressure: 250 PSI, Pressure Rating: 1000 - 2000 PSI, Pump Capacity: 500 GPM, Weight: 40 LB, Operation: Open/Closed Center

Product Details

General

Application	For Pumping Out Vaults, Trenches, Ditches, Ponds, Tanks, Pools, In A Multitude Of Industries Including Agriculture, Construction, Mining, Utilities, Public Works, Departments Of Transportation, And More
Power Source	Gerotor
Sub Brand	PUMP
Tool Type	Low Pressure Hydraulic Submersible Pumps
Type	Low Pressure Hydraulic
UPC	781810100820
UPC 12 Digit	7818101008200

Dimensions

Diameter	12 in
Weight	40 lb

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)