

HYAOF39

by Burndy
Catalog ID: HYAOF39

Prop 65 Notice

High Capacity Limiter



Product Details

General

Connector Type	Limiter
Die Index	24
Physical Attribute - Number of Holes	2
UPC	621945465763
UPC 12 Digit	6219454333666

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	2 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	1.31 in
Dimension - Pad Width inch	51 in

Conductor Related

Conductor - AL Str Size	750 kcmil
Conductor - AL Str Size Range	750 kcmil
Conductor - Copper Str Size	750 kcmil

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)