



J1252

by Burndy
Catalog ID: J1252

Prop 65 Notice

Tin plated, hard drawn copper bail designed to make hot-line clamp adapter using HYCRIMP, CABELOK, CRIMPIT or Figure 6-shaped CRIMPIT connectors.

Features: Designed To Make Hot-Line Clamp Adapter Using HYCRIMP, CABELOK CRIMPIT Or Figure 6 -Shaped CRIMPIT Connectors, Where Hot Sticks Are Used, The CABELOK CRIMPIT Or Figure 6 -Shaped CRIMPIT Are Recommended, The Line Can Be Approached With The Connector And Bail Held In The Tool, Bails Are Tin-Plated, Hard Drawn Copper, Corresponding Hycrimp: YHD-300 (3/0 - 2/0 AWG), YHD 350 (4/0 - 3/0 AWG), YHN500 (397.5 KCMIL (18-1) And 400 KCMIL (37)), Conductor Size (run - Range): 2/0 AWG - 3997.5 KCMIL, Conductor Type: ACSR, Stranded Aluminum, Solid Aluminum, Bail Size: 2/0 AWG, Shape: 6, Corresponding Cabelok Crimpit: YP28U26 (4/0 - 3/0 AWG), YP27AU26 (3/0 - 2/0 AWG), YPC33R26U (397.5 KCMIL (18-1) And 400 KCMIL (37))

Product Details

General

Application	Designed To Make Hot-Line Clamp Adapter Using HYCRIMP, CABELOK CRIMPIT Or Figure 6 -Shaped CRIMPIT Connectors
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	CONNECTOR
Type	Bail
UPC	781810014097
UPC 12 Digit	7818100140977

Dimensions

Diameter	0.38 in
Dimension - Height inch	4.25 in

Conductor Related

Conductor - ACSR Str Size	397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee kcmil
Conductor - AL Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil
Conductor - AL Str Size Range	2/0 AWG-400 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)