



K10P4CG1

by Burndy
Catalog ID: K10P4CG1

Prop 65 Notice

#14 - #4 AWG Line; #6 - #14 AWG Circuit; 10 outlets

Product Details

General

Connector Type	Neutral Bar
Material	Copper
Material - Bolt	Steel Zinc Plated
UPC	781810355497

Dimensions

Dimension - Height inch	.48 in
Dimension - Hole Size mm	12 mm
Dimension - L Length Overall mm	131 mm
Dimension - Length Overall inch	5.16 in
Dimension - Width inch	0.35 in
Dimension - Width mm	9 mm

Conductor Related

Conductor Range	#4 AWG to #14 AWG
-----------------	-------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Carton Quantity	150 EA
Minimum Pack Quantity	500

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)