



K11A30UG2

by Burndy
Catalog ID: K11A30UG2

Prop 65 Notice

Aluminum Universal Terminal, 1 Hole, Two: 6 Str.- 300 Kcmil, 3/8" Stud,, 2 Screws, Al/Cu Rated, Tin Plated

Product Details

General

Connector Type	Terminal
Material	Aluminum
Physical Attribute - Number of Holes	1
Plated	N
Plating Type	Tin plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810535752
UPC 12 Digit	7818105357522

Dimensions

Dimension - L Length Overall mm	77 mm
Dimension - Length Overall inch	3.03 in
Dimension - Stud Size inch	3/8 in
Dimension - Width inch	1.02 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size Range	6 Str.- 300 Kcmil
Conductor - Copper Str Size Range	6 Str.- 300 Kcmil
Number Of Conductors	2

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	72 EA
Minimum Pack Quantity	500

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)