



## K11A36U2N

by Burndy  
Catalog ID: K11A36U2N

Prop 65 Notice

1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing), 600 Volt Rated, Aluminum, Tin plated

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- 600 Volt Rated
- Range Taking conductor port

## Product Details

### General

Application	Terminate multiple conductors onto equipment pads, panel boards, or switchgear
Type	Bolted Lugs & Terminals
UPC	781810670149

### Dimensions

Height	3.00 in
Length	5.34 in
Width	1.50 in

### Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)