



## K12P4CG1

by Burndy  
Catalog ID: K12P4CG1

Prop 65 Notice

#14 - #4 AWG Line; #6 - #14 AWG Circuit; 12 outlets

## Product Details

### General

Connector Type	Neutral Bar
Material	Copper
Material - Bolt	Steel Zinc Plated
UPC	781810277096

### Dimensions

Dimension - Height inch	.48 in
Dimension - Hole Size mm	12 mm
Dimension - L Length Overall mm	151 mm
Dimension - Length Overall inch	5.95 in
Dimension - Width inch	0.35 in
Dimension - Width mm	9 mm

### Conductor Related

Conductor Range	#4 AWG to #14 AWG
-----------------	-------------------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	150 EA
Minimum Pack Quantity	1

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)