

# K12P6C3P1/OCAG1

by Burndy  
Catalog ID: K12P6C3P1/OCAG1

Prop 65 Notice

Dual rated Aluminum Neutral bar for copper and aluminum conductors,  
15 Circuits, 14-1/0 AWG , 14-6AWG wire range



## Product Details

### General

Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810659137
UPC 12 Digit	7818106591377

### Dimensions

Dimension - Height inch	0.62 in
Dimension - L Length Overall mm	110 mm
Dimension - Length Overall inch	4.34 in
Dimension - Width inch	0.38 in

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Size Range	(3) 14-1/0 AWG , (12) 14-6 AWG
Conductor - Copper Str Size Range	(3) 14-1/0 AWG , (12) 14-6 AWG
Number Of Conductors	15

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	150 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)