

K21A36U2N

by Burndy
Catalog ID: K21A36U2N

Prop 65 Notice

Aluminum Universal Terminal, 2 Hole, 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing), tin plated

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- 600 Volt Rated
- Range Taking conductor port



Product Details

General

| | |
|--------------------|--|
| Application | Terminate multiple conductors onto equipment pads, panel boards, or switchgear |
| Connector Type | Terminal |
| Material | Aluminum |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Type | Bolted Lugs & Terminals |
| UPC | 781810538616 |
| UPC 12 Digit | 7818105386166 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Hole Size mm | 0 mm |
| Dimension - L Length Overall mm | 0 mm |
| Dimension - Thread Size | - |
| Dimension - Width mm | 0 mm |
| Height | 3.00 in |
| Length | 5.34 in |
| Width | 2.47 in |

Electrical Ratings

| | |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Standards - RoHS Compliance Status | UI |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 65 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)