

K21A39U2N

by Burndy
Catalog ID: K21A39U2N

Prop 65 Notice

3 Cond. Panel Board with NEMA Spacing, Wire Range = 1/0 AWG - 750 kcmil; Dual Rated AL9CU; 1/2" Diameter Stud

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- 600 Volt Rated
- Range Taking conductor port



Product Details

General

Application	Terminate multiple conductors onto equipment pads, panel boards, or switchgear
Type	Bolted Lugs & Terminals
UPC	621945510180

Dimensions

Height	3.00 in
Length	5.34 in
Width	2.75 in

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)