



## K2A36UG1

by Burndy  
Catalog ID: K2A36UG1

Prop 65 Notice

Aluminum Universal Terminal, 2 Conductor, 1 Hole, 2 AWG (Str)-600 kcmil, 3/8" Stud, , 2 Screws, Al/Cu Rated, Tin Plated

## Product Details

### General

Connector Type	Terminal
Material	Aluminum
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810648414
UPC 12 Digit	7818106484144

### Dimensions

Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.2 in
Dimension - Stud Size inch	3/8 in
Dimension - Width inch	2.42 in

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Size Range	2 Str. - 600 Kcmil
Conductor - Copper Str Size Range	2 Str. - 600 Kcmil
Conductor Type	<ul style="list-style-type: none"> <li>AL C Str-Size</li> <li>CU C Str-Size</li> </ul>
Number Of Conductors	2

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B

Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Carton Quantity	72 EA
Minimum Pack Quantity	1

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)