



K2A44U

by Burndy
Catalog ID: K2A44U

Prop 65 Notice

Aluminum Universal Terminal, 2 Conductor, 1 Hole, 500-1000 kcmil, 5/8" Stud, 2 Screws, Al/Cu Rated, Tin Plated

Product Details

General

Connector Type	Terminal
Hardware Type	3/8 UNC Slotted Set Screw
Installation Torque Recommended in-lb	500 LBS/in
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Tin plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810600306
UPC 12 Digit	7818106003066

Dimensions

Dimension - Bolt Hole Size inch	0.63 in
Dimension - D inch	1.66 in
Dimension - Height fraction	2 in
Dimension - Height inch	1.95 in
Dimension - Hole Size inch	0.66 in
Dimension - Hole Size mm	17 mm
Dimension - L Length Overall mm	89 mm
Dimension - Length Overall inch	3.50 in
Dimension - N inch	0.88 in
Dimension - Pad Width inch	3.52 in
Dimension - Screw Size inch	3/8
Dimension - Stud Size inch	5/8 in
Dimension - Width fraction	3-13/25 in
Dimension - Width inch	3.52 in
Dimension - Width mm	89 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Size Range	500 -1000 Kcmil
Conductor - Copper Str Size	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	500 -1000 Kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size
Number Of Conductors	2

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
Pallet Quantity	36 EA

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)