



K2C17TN

by Burndy
Catalog ID: K2C17TN

Tin plated; Accepts 2 conductors; #10 - #7 Stranded Copper; #10 - #6 Stranded Copper; 1/4" Stud

Product Details

General

Material	Bronze Alloy, Leaded
Plated	Y
Plating Type	Tin Plated
Stud Installation Torque inch pounds	80 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810121917
UPC 12 Digit	7818101219177

Dimensions

Dimension - B Length inch	0.37 in
Dimension - Body Width inch	0.44 in
Dimension - D inch	0.50 in
Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Nut Width inch	0.62 in
Dimension - P inch	0.17 in

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG
Conductor - Copper Str Size Range	10 AWG-7 AWG
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)