



## K2C20TN

by Burndy  
Catalog ID: K2C20TN

Tin plated; Accepts 2 conductors; #10 - #5 Stranded Copper or #10 - #4 Solid Copper; 5/16" Stud

## Product Details

### General

Material	Bronze Alloy, Leaded
Plated	Y
Plating Type	Tin Plated
Stud Installation Torque inch pounds	180 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC 12 Digit	0

### Dimensions

Dimension - B Length inch	0.41 in
Dimension - Body Width inch	0.50 in
Dimension - D inch	0.62 in
Dimension - Height inch	1.06 in
Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.62 in
Dimension - Nut Width inch	0.69 in
Dimension - P inch	0.22 in

### Conductor Related

Conductor - Copper Solid Size	10;9;8;7;6;5;4
Conductor - Copper Solid Size Range	10-4
Conductor - Copper Str Size	10;9;8;7;6;5
Conductor - Copper Str Size Range	10-5
Physical Attribute - Number of Conductors Accommodated Total	2

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)