



K2C22B1TN

by Burndy
Catalog ID: K2C22B1TN

Prop 65 Notice

Tin plated; Accepts 2 conductors; #10 - #2 Copper Solid; #10 - #3 Copper Stranded; 3/8" Stud

Product Details

General

Material	Bronze Alloy, Leaded
Plated	Y
Plating Type	Tin Plated
Stud Installation Torque inch pounds	280 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810110621
UPC 12 Digit	7818101106211

Dimensions

Dimension - B Length inch	0.96 in
Dimension - Body Width inch	0.62 in
Dimension - D inch	1.12 in
Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Nut Width inch	0.75 in
Dimension - P inch	0.26 in

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG
Conductor - Copper Str Size Range	10 AWG-3 AWG
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)