



K2C22TN

by Burndy
Catalog ID: K2C22TN

Tin plated; Accepts 2 conductors; #10 - #2 Copper Solid; #10 - #3 Copper Stranded; 3/8" Stud

Product Details

General

| | |
|--------------------------------------|----------------------|
| Material | Bronze Alloy, Leaded |
| Plated | Y |
| Plating Type | Tin Plated |
| Stud Installation Torque inch pounds | 280 LBS/in |
| Trade Name | SERVIT POST™ |
| Type | KC and K2C Series |
| UPC | 781810110638 |
| UPC 12 Digit | 7818101106388 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 1.25 in |
| Dimension - Body Width inch | 0.62 in |
| Dimension - D inch | 0.62 in |
| Dimension - Height inch | 1.25 in |
| Dimension - L Length Overall mm | 87.6 mm |
| Dimension - Length Overall inch | 3.45 in |
| Dimension - Nut Width inch | 0.75 in |
| Dimension - P inch | 0.26 in |

Conductor Related

| | |
|--|--|
| Conductor - Copper Solid Size | 10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG |
| Conductor - Copper Solid Size Range | 10 AWG-2 AWG |
| Conductor - Copper Str Size | 10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG |
| Conductor - Copper Str Size Range | 10 AWG-3 AWG |
| Physical Attribute - Number of Conductors Accommodated Total | 2 |

Certifications and Compliance

| | |
|---|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |

| | |
|------------------------------------|-------|
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)