



K2C23

by Burndy
Catalog ID: K2C23

Prop 65 Notice

Mechanical Grounding Connector, Cable to Flat, 8-2 AWG (Str) / 10-1 AWG (Sol), 3/8" Stud, cross base flat :.62.

Features: SERVIT POST Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar, One-Wrench Installation, For 1 Or 2 Conductors, Conductor Type: Run: Commercial Stranded Copper, Commercial Solid Copper, Stud/bolt Size: 3/8-16 Diameter, 15/32 IN Length, Height: 2 IN, Cross Flats: 13/16, 5/8 IN

Product Details

General

Application	For Direct Burial Applications And Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar
Material	Bronze Alloy, Leaded
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	280 LBS/in
Sub Brand	SERVIT POST
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810257203
UPC 12 Digit	7818102572033

Dimensions

Dimension - B Length fraction	15/32 in
Dimension - B Length inch	0.46 in
Dimension - Body Width inch	0.62 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	0.62 in
Dimension - Height fraction	1
Dimension - Height inch	1.34 in
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.19 in
Dimension - Nut Width inch	0.81 in
Dimension - P inch	0.32 in
Dimension - Threads per inch	16
Dimension - Width inch	34 mm

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Size Range	1 AWG - 10 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	2 AWG - 8 AWG
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)