



K2C25TN

by Burndy
Catalog ID: K2C25TN

Prop 65 Notice

Tin plated; Accepts 2 conductors; #2 - 1/0 Stranded Copper; #2 - 2/0 Solid Copper; 1/2" Stud

Product Details

General

Material	Bronze Alloy, Leaded
Plated	Y
Plating Type	Tin Plated
Stud Installation Torque inch pounds	180 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810091609
UPC 12 Digit	7818100916099

Dimensions

Dimension - B Length inch	0.53 in
Dimension - Body Width inch	0.75 in
Dimension - D inch	0.75 in
Dimension - Height inch	1.56 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.31 in
Dimension - Nut Width inch	0.93 in
Dimension - P inch	0.39 in

Conductor Related

Conductor - Copper Solid Size	2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Size Range	2 AWG-1/0 AWG
Conductor - Copper Str Size	2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	2 AWG-1/0
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)