



K2C26B1TN

by Burndy
Catalog ID: K2C26B1TN

Prop 65 Notice

Tin plated; Accepts 2 conductors; #2 - 2/0 Stranded Copper; #2 - 3/0 Solid Copper; 1/2" Stud

Product Details

General

Material	Bronze Alloy, Leaded
Plated	Y
Plating Type	Tin Plated
Stud Installation Torque inch pounds	480 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810091470
UPC 12 Digit	7818100914700

Dimensions

Dimension - B Length inch	1.04 in
Dimension - Body Width inch	0.88 in
Dimension - D inch	1.25 in
Dimension - Height inch	1.81 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.09 in
Dimension - Nut Width inch	1.04 in
Dimension - P inch	0.44 in

Conductor Related

Conductor - Copper Solid Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Size Range	2 AWG-3/0 AWG
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	2 AWG-2/0 AWG
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)