



## K2C34

by Burndy  
Catalog ID: K2C34

Prop 65 Notice

Mechanical Grounding Connector, 2 Cables to Flat, 3/0 AWG - 500 kcmil (Str), 3/4" Stud.

Features: SERVIT POST Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar, One-Wrench Installation, Cross Flats: 2, 1-5/8 IN, Conductor Type: Run: Commercial Stranded Copper, Height: 4-1/2 IN, Dimension B: 1 IN, Stud Size: 3/4-10

## Product Details

### General

Application	For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	1050 LBS/in
Sub Brand	SERVIT POST
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810257708
UPC 12 Digit	7818102577088

### Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	0.99 in
Dimension - Body Width inch	1.62 in
Dimension - Bolt Size fraction	3/4
Dimension - D inch	1.25 in
Dimension - Height fraction	2-3/8
Dimension - Height inch	2.38 in
Dimension - L Length Overall mm	91.9 mm
Dimension - Length Overall inch	3.62 in
Dimension - Nut Width inch	2.00 in
Dimension - P inch	0.85 in
Dimension - Threads per inch	10

### Conductor Related

Conductor - Copper Str Size	3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	3/0 AWG-500 kcmil

Physical Attribute - Number of Conductors Accommodated Total	2
--	---

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)