



K3A26U2N

by Burndy
Catalog ID: K3A26U2N

Prop 65 Notice

Aluminum Universal Terminal, 3 Conductor, 2 Hole, 14-2/0 AWG (Str), 1/2" Stud, 1.75" Stud Hole Spacing, 3 Screws, Al/Cu Rated, Tin Plated.

Universal terminal, Dual-rated three conductor lugs are constructed from high strength aluminum alloy and electro tin-plated to provide low contact resistance

Product Details

General

Application	For Aluminum and Copper Conductors
Connector Type	Terminal
Installation Torque Recommended in-lb	50 LBS/in
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810601051
UPC 12 Digit	7818106010511

Dimensions

Dimension - Bolt Hole Size inch	0.57 in
Dimension - D inch	3.06 in
Dimension - Height fraction	1.8 in
Dimension - Height inch	1.79 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.97 in
Dimension - Stud Size inch	1/2 in
Dimension - Width fraction	1-19/20 in

Dimension - Width inch	1.97 in
Dimension - Width mm	50 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	14 Str.-2/0 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	14 Str.-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size
Number Of Conductors	3

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	108 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)