

K5P6C2P1/OCAG1

by Burndy
Catalog ID: K5P6C2P1/OCAG1

Prop 65 Notice

Aluminum Neutral Bar



Product Details

General

Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Temperature Rating	194° F
UPC	781810665572
UPC 12 Digit	7818106655722

Dimensions

Dimension - Height inch	0.62 in
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.26 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size Range	1/0 AWG - 14 AWG
Conductor - Copper Str Size Range	1/0 AWG - 14 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	150 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)