



KA252TC38

by Burndy
Catalog ID: KA252TC38

Prop 65 Notice

Cast Copper Alloy KA-Lug, 4 Str. - 1/0 Str., 3/8.

Features: Compact, Economical, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks, Dimension K: 27/64 IN, Dimension N: 3/8 IN, Dimension T: 1/8 IN, Tongue Width: 3/4 IN, Installation Torque: 200 IN-LB, Height: 15/16 IN, Length: 2-13/16 IN, Stud/bolt Hole Size: 3/8 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks
Connector Type	Terminal
Hardware Type	1 / 2 "
Installation Torque Recommended in-lb	200 LBS/in
Material	Copper Alloy, Cast
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	KA-LUG
Temperature Rating	194° F
Trade Name	KA-LUG™
Type	Bolted Lugs & Terminals
UPC	781810034057
UPC 12 Digit	7818100340577

Dimensions

Dimension - B Length fraction	20/29 in
Dimension - B Length inch	0.69 in
Dimension - Height fraction	15/16
Dimension - Height inch	0.94 in
Dimension - Hole Size fraction	27/64
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.69 in
Dimension - N inch	0.38 in
Dimension - Pad Width inch	0.75 in

Dimension - Stud Size inch	3/8
----------------------------	-----

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	4 AWG-1/0
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)