



KA25UAR

by Burndy
Catalog ID: KA25UAR

Prop 65 Notice

Dual Rated for copper and aluminum; aluminum alloy; tin plated; bottom anti-rotational tab; 1/4" stud hole; #14 - 1/0 AWG Al/Cu; CSA Certified, UL Listed

Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	50 LBS/in
Material	Aluminum
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370865

Dimensions

Dimension - D inch	1.47 in
Dimension - Height fraction	64/81 in
Dimension - Height inch	0.81 in
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.47 in
Dimension - Stud Size fraction	1/4
Dimension - Width inch	0.63 in
Dimension - Width mm	16 mm

Conductor Related

Conductor - AL Str Size	14;12;10;8;6;4;3;2;1;0
Conductor - AL Str Size Range	14-1/0
Conductor - Copper Str Size	14;12;10;9;8;7;6;5;4;3;2;1;0
Conductor - Copper Str Size Range	14-1/0
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	150 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)