



## KA28H

by Burndy  
Catalog ID: KA28H

Copper Terminal, #1 - 4/0 Stranded; 3/8" Stud; 275 lb-in recommended torque

### Product Details

#### General

Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Allen
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810528402

#### Dimensions

Dimension - B Length inch	0.81 in
Dimension - Height inch	1.25 in
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - N inch	0.44 in
Dimension - Pad Width inch	0.94 in

#### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

#### Conductor Related

Conductor - Copper Str Size Range	# 1Str. - 4/0 Str.
Number Of Wires	1

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)