



KA28

by Burndy
Catalog ID: KA28

Prop 65 Notice

Copper Terminal, 1 Hole, 1-4/0 AWG (Str), 3/8" Stud, 1 Screw.

Features: Compact, Economical, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks, Dimension N: 7/16 IN, Dimension K: 27/64 IN, Dimension T: 3/16 IN, Tongue Width: 1-15/16 IN, Installation Torque: 275 IN-LB, Stud/bolt Hole Size: 3/8 IN, Height: 1-1/4 IN, Length: 1-15/16 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks
Connector Type	Terminal
Hardware Type	5 / 8 "
Installation Torque Recommended in-lb	275 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	KA-LUG
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810364857

Dimensions

Dimension - B Length fraction	64/79 in
Dimension - B Length inch	0.81 in
Dimension - Height fraction	1-1/4 in
Dimension - Height inch	1.25 in
Dimension - Hole Size fraction	27/64
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - N inch	0.44 in
Dimension - Pad Width inch	0.94 in
Dimension - Stud Size inch	3/8

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	1 AWG-4/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)